

# 19" Front Panel

Front panels made of Aluminum.



## CERTIFICATIONS



## FEATURES

Aluminum, 4 or 3 mm thick, with Anodized or Painted finish

## SPECIFICATIONS

- Rack Width:** 95HP
- Material:** Aluminum
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/2

| Catalog Number | Rack Height | Depth (D) | Mounting       | Finish        | Front Finish | Package Quantity |
|----------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 30118-948      | 1U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-299      | 1U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 40304-074      | 1U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-098      | 1U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-954      | 7U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |

| Catalog Number | Rack Height | Depth (D) | Mounting       | Finish        | Front Finish | Package Quantity |
|----------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 30118-955      | 8U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-953      | 6U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-305      | 6U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-952      | 5U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30219-113      | 6U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-104      | 3U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-949      | 2U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-303      | 4U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-309      | 10U         | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 40304-079      | 6U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-307      | 8U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 40304-077      | 4U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-304      | 5U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-306      | 7U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-301      | 2U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |

Table 2/2

| Catalog Number | Rack Height | Depth (D) | Mounting       | Finish        | Front Finish | Package Quantity |
|----------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 40304-076      | 3U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 40304-082      | 9U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-137      | 7U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 40304-080      | 7U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-143      | 9U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-951      | 4U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-308      | 9U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30118-956      | 9U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30219-107      | 4U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-144      | 10U         | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 40304-081      | 8U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30219-138      | 8U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-950      | 3U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30219-110      | 5U          | 3mm       | Screw-on Front | Powder Coated | Anodized     | 1                |
| 30118-302      | 3U          | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |
| 30219-101      | 2U          | 3mm       | Screw-on Front | Anodized      | Anodized     | 1                |

| Catalog Number | Rack Height | Depth (D) | Mounting       | Finish        | Front Finish | Package Quantity |
|----------------|-------------|-----------|----------------|---------------|--------------|------------------|
| 40304-083      | 10U         | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 40304-075      | 2U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 40304-078      | 5U          | 4mm       | Screw-on Front | Anodized      | Anodized     | 1                |
| 30118-957      | 10U         | 3mm       | Screw-on Front | Powder Coated | Painted      | 1                |

Table 1/2

| Catalog Number | Rear Finish | Treated Edges | Color Code | EMC Shielding | Height (H) | Type            |
|----------------|-------------|---------------|------------|---------------|------------|-----------------|
| 30118-948      | Painted     |               | RAL 7021   | No            | 43.6mm     | 19" Front Panel |
| 30118-299      | Painted     |               | RAL 7035   | No            | 43.6mm     | 19" Front Panel |
| 40304-074      | Anodized    | Yes           |            | No            | 43.6mm     | 19" Front Panel |
| 30219-098      | Anodized    | No            |            | No            | 43.6mm     | 19" Front Panel |
| 30118-954      | Painted     |               | RAL 7021   | No            | 310.3mm    | 19" Front Panel |
| 30118-955      | Painted     |               | RAL 7021   | No            | 354.8mm    | 19" Front Panel |
| 30118-953      | Painted     |               | RAL 7021   | No            | 265.9mm    | 19" Front Panel |
| 30118-305      | Painted     |               | RAL 7035   | No            | 265.9mm    | 19" Front Panel |
| 30118-952      | Painted     |               | RAL 7021   | No            | 221.4mm    | 19" Front Panel |
| 30219-113      | Anodized    | No            |            | No            | 265.9mm    | 19" Front Panel |
| 30219-104      | Anodized    | No            |            | No            | 132.5mm    | 19" Front Panel |
| 30118-949      | Painted     |               | RAL 7021   | No            | 88.1mm     | 19" Front Panel |
| 30118-303      | Painted     |               | RAL 7035   | No            | 177mm      | 19" Front Panel |
| 30118-309      | Painted     |               | RAL 7035   | No            | 443.7mm    | 19" Front Panel |
| 40304-079      | Anodized    | Yes           |            | No            | 265.9mm    | 19" Front Panel |
| 30118-307      | Painted     |               | RAL 7035   | No            | 354.8mm    | 19" Front Panel |
| 40304-077      | Anodized    | Yes           |            | No            | 177mm      | 19" Front Panel |
| 30118-304      | Painted     |               | RAL 7035   | No            | 221.4mm    | 19" Front Panel |
| 30118-306      | Painted     |               | RAL 7035   | No            | 310.3mm    | 19" Front Panel |
| 30118-301      | Painted     |               | RAL 7035   | No            | 88.1mm     | 19" Front Panel |

Table 2/2

| Catalog Number | Rear Finish | Treated Edges | Color Code | EMC Shielding | Height (H) | Type            |
|----------------|-------------|---------------|------------|---------------|------------|-----------------|
| 40304-076      | Anodized    | Yes           |            | No            | 132.5mm    | 19" Front Panel |
| 40304-082      | Anodized    | Yes           |            | No            | 399.2mm    | 19" Front Panel |
| 30219-137      | Anodized    | No            |            | No            | 310.3mm    | 19" Front Panel |
| 40304-080      | Anodized    | Yes           |            | No            | 310.3mm    | 19" Front Panel |

| Catalog Number | Rear Finish | Treated Edges | Color Code | EMC Shielding | Height (H) | Type            |
|----------------|-------------|---------------|------------|---------------|------------|-----------------|
| 30219-143      | Anodized    | No            |            | No            | 399.2mm    | 19" Front Panel |
| 30118-951      | Painted     |               | RAL 7021   | No            | 177mm      | 19" Front Panel |
| 30118-308      | Painted     |               | RAL 7035   | No            | 399.2mm    | 19" Front Panel |
| 30118-956      | Painted     |               | RAL 7021   | No            | 399.2mm    | 19" Front Panel |
| 30219-107      | Anodized    | No            |            | No            | 177mm      | 19" Front Panel |
| 30219-144      | Anodized    | No            |            | No            | 443.7mm    | 19" Front Panel |
| 40304-081      | Anodized    | Yes           |            | No            | 354.8mm    | 19" Front Panel |
| 30219-138      | Anodized    | No            |            | No            | 354.8mm    | 19" Front Panel |
| 30118-950      | Painted     |               | RAL 7021   | No            | 132.5mm    | 19" Front Panel |
| 30219-110      | Anodized    | No            |            | No            | 221.4mm    | 19" Front Panel |
| 30118-302      | Painted     |               | RAL 7035   | No            | 132.5mm    | 19" Front Panel |
| 30219-101      | Anodized    | No            |            | No            | 88.1mm     | 19" Front Panel |
| 40304-083      | Anodized    | Yes           |            | No            | 443.7mm    | 19" Front Panel |
| 40304-075      | Anodized    | Yes           |            | No            | 88.1mm     | 19" Front Panel |
| 40304-078      | Anodized    | Yes           |            | No            | 221.4mm    | 19" Front Panel |
| 30118-957      | Painted     |               | RAL 7021   | No            | 443.7mm    | 19" Front Panel |

Table 1/2

| Catalog Number | Width (W) |
|----------------|-----------|
| 30118-948      | 483mm     |
| 30118-299      | 483mm     |
| 40304-074      | 483mm     |
| 30219-098      | 483mm     |
| 30118-954      | 483mm     |
| 30118-955      | 483mm     |
| 30118-953      | 483mm     |
| 30118-305      | 483mm     |
| 30118-952      | 483mm     |
| 30219-113      | 483mm     |
| 30219-104      | 483mm     |
| 30118-949      | 483mm     |
| 30118-303      | 483mm     |
| 30118-309      | 483mm     |
| 40304-079      | 483mm     |

| Catalog Number | Width (W) |
|----------------|-----------|
| 30118-307      | 483mm     |
| 40304-077      | 483mm     |
| 30118-304      | 483mm     |
| 30118-306      | 483mm     |
| 30118-301      | 483mm     |

Table 2/2

| Catalog Number | Width (W) |
|----------------|-----------|
| 40304-076      | 483mm     |
| 40304-082      | 483mm     |
| 30219-137      | 483mm     |
| 40304-080      | 483mm     |
| 30219-143      | 483mm     |
| 30118-951      | 483mm     |
| 30118-308      | 483mm     |
| 30118-956      | 483mm     |
| 30219-107      | 483mm     |
| 30219-144      | 483mm     |
| 40304-081      | 483mm     |
| 30219-138      | 483mm     |
| 30118-950      | 483mm     |
| 30219-110      | 483mm     |
| 30118-302      | 483mm     |
| 30219-101      | 483mm     |
| 40304-083      | 483mm     |
| 40304-075      | 483mm     |
| 40304-078      | 483mm     |
| 30118-957      | 483mm     |

## ADDITIONAL PRODUCT DETAILS

---

Please order 19" assembly kit separately.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**