ProLine Joining Subpanel

Provides a continuous panel surface in multiple bay enclosures. The joining subpanel is inserted between full subpanels of equal height. It can be installed from front or rear.

FEATURES

Holes for grounding and mounting hardware are provided.

SPECIFICATIONS

Thickness: 2.66mm

Table 1/1

Catalog Number	Article Number	Material	Color	Finish
PJP7G	28749	Mild Steel		Galvanized
PJP22G	28799	Mild Steel		Galvanized
PJP16	99380	Mild Steel	White	Powder Coated
PJP20G	28789	Mild Steel		Galvanized
PJP20	99400	Mild Steel	White	Powder Coated
PJP16G	28769	Mild Steel		Galvanized
PJP22	99410	Mild Steel	White	Powder Coated
PJP18	99390	Mild Steel	White	Powder Coated
PJP18G	28779	Mild Steel		Galvanized

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.