


DIN Rail

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



FEATURES

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFICATIONS

Product Type: DIN Rail

Table 1/2

| Catalog Number | Material | Height | Length | Finish | Package Quantity | Depth |
|----------------|----------|--------|--------|-------------|------------------|-------|
| 20118-879 | Steel | 35mm | 175mm | Zinc Plated | 4 | 7.5mm |
| 20118-874 | Steel | 35mm | 275mm | Zinc Plated | 4 | 15mm |
| 20118-872 | Steel | 35mm | 125mm | Zinc Plated | 4 | 15mm |
| 20118-883 | Steel | 35mm | 575mm | Zinc Plated | 4 | 7.5mm |
| 20118-875 | Steel | 35mm | 375mm | Zinc Plated | 4 | 15mm |
| 20118-878 | Steel | 35mm | 125mm | Zinc Plated | 4 | 7.5mm |
| 20118-880 | Steel | 35mm | 275mm | Zinc Plated | 4 | 7.5mm |
| 20118-877 | Steel | 35mm | 575mm | Zinc Plated | 4 | 15mm |
| 20118-882 | Steel | 35mm | 475mm | Zinc Plated | 4 | 7.5mm |
| 20118-873 | Steel | 35mm | 175mm | Zinc Plated | 4 | 15mm |
| 20118-881 | Steel | 35mm | 375mm | Zinc Plated | 4 | 7.5mm |

| Catalog Number | Material | Height | Length | Finish | Package Quantity | Depth |
|----------------|----------|--------|--------|-------------|------------------|-------|
| 20118-876 | Steel | 35mm | 475mm | Zinc Plated | 4 | 15mm |
| 20118-893 | Steel | 35mm | 375mm | Zinc Plated | 10 | 7.5mm |
| 20118-892 | Steel | 35mm | 275mm | Zinc Plated | 10 | 7.5mm |
| 20118-891 | Steel | 35mm | 175mm | Zinc Plated | 10 | 7.5mm |
| 20118-890 | Steel | 35mm | 125mm | Zinc Plated | 10 | 7.5mm |
| 20118-895 | Steel | 35mm | 575mm | Zinc Plated | 10 | 7.5mm |
| 20118-894 | Steel | 35mm | 475mm | Zinc Plated | 10 | 7.5mm |
| 20118-889 | Steel | 35mm | 575mm | Zinc Plated | 10 | 15mm |
| 20118-887 | Steel | 35mm | 375mm | Zinc Plated | 10 | 15mm |

Table 2/2

| Catalog Number | Material | Height | Length | Finish | Package Quantity | Depth |
|----------------|----------|--------|--------|-------------|------------------|-------|
| 20118-885 | Steel | 35mm | 175mm | Zinc Plated | 10 | 15mm |
| 20118-886 | Steel | 35mm | 275mm | Zinc Plated | 10 | 15mm |
| 20118-884 | Steel | 35mm | 125mm | Zinc Plated | 10 | 15mm |
| 20118-888 | Steel | 35mm | 475mm | Zinc Plated | 10 | 15mm |

Table 1/2

| Catalog Number | Width |
|----------------|-------|
| 20118-879 | 175mm |
| 20118-874 | 275mm |
| 20118-872 | 125mm |
| 20118-883 | 575mm |
| 20118-875 | 375mm |
| 20118-878 | 125mm |
| 20118-880 | 275mm |
| 20118-877 | 575mm |
| 20118-882 | 475mm |
| 20118-873 | 175mm |
| 20118-881 | 375mm |
| 20118-876 | 475mm |
| 20118-893 | 375mm |
| 20118-892 | 275mm |
| 20118-891 | 175mm |

| Catalog Number | Width |
|----------------|-------|
| 20118-890 | 125mm |
| 20118-895 | 575mm |
| 20118-894 | 475mm |
| 20118-889 | 575mm |
| 20118-887 | 375mm |

Table 2/2

| Catalog Number | Width |
|----------------|-------|
| 20118-885 | 175mm |
| 20118-886 | 275mm |
| 20118-884 | 125mm |
| 20118-888 | 475mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE