


# PropacPRO Front Panel, Full Width, Unshielded



The front panel, full width for PropacPRO Case mounts to the frame of the case.

## CERTIFICATIONS



## FEATURES

Al panel, 2.0 mm (84 HP 2.5 mm)

## SPECIFICATIONS

- Material:** Aluminum
- Finish:** Anodized
- Accessory Type:** Front panel
- Product Type:** Front Panel

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
20850-136	3U	63HP	1	Anodized	Anodized	No
20850-158	6U	84HP	1	Anodized	Conductive	No
20850-129	2U	63HP	1	Anodized	Anodized	No
20850-135	3U	42HP	1	Anodized	Anodized	No
20850-142	4U	42HP	1	Anodized	Anodized	No
20850-143	4U	63HP	1	Anodized	Anodized	No
20850-130	2U	84HP	1	Anodized	Anodized	No

Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges
20850-144	4U	84HP	1	Anodized	Anodized	No
20850-134	3U	28HP	1	Anodized	Anodized	No
20850-128	2U	42HP	1	Anodized	Anodized	No
20850-137	3U	84HP	1	Anodized	Anodized	No

Table 2/2

Catalog Number	Depth	Height	Width
20850-136	2mm	128.5mm	345.4mm
20850-158	2.5mm	261.8mm	452mm
20850-129	2mm	84mm	345.4mm
20850-135	2mm	128.5mm	238.7mm
20850-142	2mm	172.9mm	238.7mm
20850-143	2mm	172.9mm	345.4mm
20850-130	2.5mm	84mm	452mm
20850-144	2.5mm	172.9mm	452mm
20850-134	2mm	128.5mm	167.6mm
20850-128	2mm	84mm	238.7mm
20850-137	2.5mm	128.5mm	452mm

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**