

Syspend 281-MAX Flex Base



Syspend 281-MAX Flex Base offers a pedestal solution for operator stations to give flexible positions, manoeuvrability, and also stability in production. Choose the correct adapter plate for your application needs.

FEATURES

Mount Casters to the bottom to roll around Flex Base

Mount Adjustable Feet to the bottom to help secure the Flex Base

Maximum of 4 additional weights can be installed to help stabilize the Flex base

Integrated earthing screws

Plenty of space for cable routing

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Material | Finish |
|----------------|----------------|--------|-------|-------|----------|---------------|
| S2MFBG | 59357 | 591mm | 591mm | 72mm | Aluminum | Powder Coated |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE