

MTSH Spring Toggle with Hook



FEATURES

For fixing into hollow walls, hollow ceilings and suspended ceilings

Washer, nut and toggle included

SPECIFICATIONS

Table 1/2						
Catalog Number	Article Number	Material	Finish	Rod Size (RS)	Length (L)	Drill Bit Diameter
MTSH4	584430	Steel	Electrogalvanized	4	70mm	14mm


Table 2/2		
Catalog Number	Article Number	Ultimate Static Load (F)
MTSH4	584430	300N

ADDITIONAL PRODUCT DETAILS

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.

Spring toggle requires a minimum clearance of 35 mm (1.38") to open when installed.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

