

Cable to Web of Rail Complete Welder, Power, UIC60, 50 mm² Concentric, Right Hand

Data Solutions

CATALOG NUMBER

PBWH301RH



FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

Material: Graphite; Steel; Thermoplastic

Rail Type: UIC60

Bond Terminal Style: W

Conductor Size: 50 mm² Concentric

Conductor Outer Diameter, Nominal: 8.89mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBWX5LH

Welding Material: PB65, Sold Separately

Handle Clamp: C105C, Sold Separately

Conductor Sleeve: S05F, Sold Separately

Hammer Die: WD80, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE