

Socket Strip, IEC C19

Data Solutions

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C19 outlets.



CERTIFICATIONS



FEATURES

Socket strips with C19 IEC sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m, with connector in accordance with IEC 60309

Mounting height 1 U

SPECIFICATIONS

Material: Aluminum; Polyamide

Color: Grey

Product Type: Socket Strip

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|----------------|-------------|-----------------|------------------|------------|------------------|-------|
| 60110-280 | IEC C19 | 8 | No | 230V | 1 | 44mm |

| CatalogNumber | Socket Type | SocketQuantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|---------------|-------------|----------------|------------------|------------|------------------|-------|
| 60110-282 | IEC C19 | 12 | No | 230V | 1 | 44mm |
| 60110-281 | IEC C19 | 12 | No | 230V | 1 | 44mm |

Table 2/2

| Catalog Number | Finish | Height | Length |
|----------------|----------|--------|---------|
| 60110-280 | Anodized | 44mm | 438.5mm |
| 60110-282 | Anodized | 44mm | 947.5mm |
| 60110-281 | Anodized | 44mm | 947.5mm |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE