

MSP0 PDU, 2U, 60A(48A), 208V, 3P Delta, 6 CB, (9)C13, (9)4-in-1

Data Solutions

CATALOG NUMBER

EN6963



The Advantage Series Outlet Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at the input phase, circuit breaker, and individual outlet levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

PRODUCT ATTRIBUTES

Product Family: Enlogic

Product Type: Socket Strip

Socket Type: (9) C13/C15; (9) C13/C15/C19/C21

Circuit Breaker: 20 A

Color: Black

Circuit Breaker Quantity: 6

Switched Outlets: Yes

Length: 87mm

Power Rating: 17.3 kVA

Interrupt Rating: 10kAIC

Number of Poles: 2

Input Voltage: 208V

Phase: 3 PH Delta

Output Voltage: 208VAC

Plug Type: IEC 60309 460P9 (IP44)

Nominal Voltage: 208V

Removable Input Cable: No

Amperage (Derated Amperage): 60 A (48 A)

Rack Units: 2U

Type: Intelligent PDU

Finish: Powder Coated

Metering Type: Outlet

Material: Steel

Height: 87mm

Weight: 9kg

Width: 444mm

Depth: 269mm

Package Quantity: 1

Input Cable Length: 1.8m

ADDITIONAL PRODUCT DETAILS

87 mm L x 444 mm W x 269 mm D, (269 mm D at CB)

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE