

# Heavy Duty Pipe Clamp per DIN 3567, Steel, Plain, 139.7mm OD, 5" Pipe, 125 DN

## CATALOG NUMBER

**DIN140PL**



## FEATURES

- For high static requirements in industrial construction
- Suitable for fix point applications
- Can be welded onto T-beam to form a sliding element

## PRODUCT ATTRIBUTES

Article Number: 400171

Material: Steel

Finish: Plain

Outer Diameter (OD): 139.7 mm

Pipe Size: 5"

NB/DN: 125

Hole Size (HS): 18 mm

Width (W): 50 mm

Thickness (T): 8 mm

A: 204 mm

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

