

# Enlogic Basic PDU

## Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

### FEATURES

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

### SPECIFICATIONS

Table 1/6

Catalog Number	Product Family	Type	Product Type	Socket Type	Socket Quantity	Color
EB0860	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black
EB09JA	Enlogic	Basic PDU	Socket Strip	(18) C13/C15, (18) C13/C15/C19/C21	36	Black
EB0360	Enlogic	Basic PDU	Socket Strip	(16) C13/C15	20	Black

Table 2/6

Catalog Number	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Interrupt Rating
EB0860	No	3000mm	20 A, 1-pole, Hy-MagA	17.3 kVA North America, 22.1 kVA International	6	

CatalogNumber	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	InterruptRating
EB09JA	No	1800mm	20 A, 1-pole, Hy-MagA	34.6 kVA North America, 43.5 kVA International	12	
EB0360	No	3000mm	16 A, 1-pole, Hy-Mag	7.4 kVA	2	5kAIC

Table 3/6

Catalog Number	Nominal Power Output	Nominal Voltage	Number of Output Voltages	Number of Phases	On/Off Switch Included	Amperage (Derated Amperage)
EB0860	230VAC	415V			No	30 A (24 A) North America, 32 A International
EB09JA	230VAC	415V	36		No	60 A (48 A) North America, 63 A International
EB0360	230VAC	230V	20	1	No	32 A

Table 4/6

Catalog Number	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Material
EB0860	208 – 230VAC	0U	IEC 60309 530P6/532P6	None	No	Steel
EB09JA	208 – 230VAC	0U	IEC 60309 560P6/563P6	None	No	Steel
EB0360	230VAC	0U	IEC 60309 332P6 (IP44)	None	No	Steel

Table 5/6

Catalog Number	Finish	Height	Width	Depth	Weight	Package Quantity
EB0860	Powder Coated	1490mm	56mm	55mm		1
EB09JA	Powder Coated	965mm	114mm	75mm		1
EB0360	Powder Coated	817mm	52mm	53mm	3.6kg	1

Table 6/6

Catalog Number	Input Cable Length
EB0860	3m
EB09JA	1.8m

Catalog Number	Input Cable Length
EB0360	3m

## ADDITIONAL PRODUCT DETAILS

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**