

Threaded Rod



FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material | Finish | Quality Class | Rod Size (RS) | Length (L) |
|----------------|----------------|---------------------------------|--------------------|---------------|---------------|------------|
| 050M61000S4 | 592700 | Stainless Steel 304 (EN 1.4301) | | 70 | M6 | 1000mm |
| 050M61000 | 592570 | Steel | Electrogalvanized | 4.8 | M6 | 1000mm |
| 050M101000S4 | 592740 | Stainless Steel 304 (EN 1.4301) | | 70 | M10 | 1000mm |
| 050M121000 | 592630 | Steel | Electrogalvanized | 4.8 | M12 | 1000mm |
| 050M161000 | 400332 | Steel | Electrogalvanized | 4.8 | M16 | 1000mm |
| 050M101000HD | 592615 | Steel | Hot-Dip Galvanized | 4.8 | M10 | 1000mm |

| Catalog Number | Article Number | Material | Finish | Quality Class | Rod Size (RS) | Length (L) |
|----------------|----------------|---------------------------------|--------------------|---------------|---------------|------------|
| 050M81000S4 | 592720 | Stainless Steel 304 (EN 1.4301) | | 70 | M8 | 1000mm |
| 050M121000HD | 592635 | Steel | Hot-Dip Galvanized | 4.8 | M12 | 1000mm |
| 050M81000 | 592590 | Steel | Electrogalvanized | 4.8 | M8 | 1000mm |
| 050M121000S4 | 592760 | Stainless Steel 304 (EN 1.4301) | | 70 | M12 | 1000mm |
| 050M101000 | 592610 | Steel | Electrogalvanized | 4.8 | M10 | 1000mm |
| 050M122000 | 592640 | Steel | Electrogalvanized | 4.8 | M12 | 2000mm |
| 050M82000 | 592600 | Steel | Electrogalvanized | 4.8 | M8 | 2000mm |
| 050M103000 | 592670 | Steel | Electrogalvanized | 4.8 | M10 | 3000mm |
| 050M62000 | 592580 | Steel | Electrogalvanized | 4.8 | M6 | 2000mm |
| 050M63000 | 592650 | Steel | Electrogalvanized | 4.8 | M6 | 3000mm |
| 050M123000 | 592680 | Steel | Electrogalvanized | 4.8 | M12 | 3000mm |
| 050M102000 | 592620 | Steel | Electrogalvanized | 4.8 | M10 | 2000mm |
| 050M83000 | 592660 | Steel | Electrogalvanized | 4.8 | M8 | 3000mm |
| 050M82000S4 | 592730 | Stainless Steel 304 (EN 1.4301) | | 70 | M8 | 2000mm |

Table 2/2

| Catalog Number | Article Number | Material | Finish | Quality Class | Rod Size (RS) | Length (L) |
|----------------|----------------|---------------------------------|--------|---------------|---------------|------------|
| 050M62000S4 | 592710 | Stainless Steel 304 (EN 1.4301) | | 70 | M6 | 2000mm |
| 050M102000S4 | 592750 | Stainless Steel 304 (EN 1.4301) | | 70 | M10 | 2000mm |

Table 1/2

| Catalog Number | Article Number | Static Load |
|----------------|----------------|-------------|
| 050M61000S4 | 592700 | 2400N |
| 050M61000 | 592570 | 2400N |
| 050M101000S4 | 592740 | 7000N |
| 050M121000 | 592630 | 10000N |
| 050M161000 | 400332 | 18000N |
| 050M101000HD | 592615 | 7000N |
| 050M81000S4 | 592720 | 4500N |
| 050M121000HD | 592635 | 10000N |
| 050M81000 | 592590 | 4500N |
| 050M121000S4 | 592760 | 10000N |
| 050M101000 | 592610 | 7000N |
| 050M122000 | 592640 | 10000N |
| 050M82000 | 592600 | 4500N |
| 050M103000 | 592670 | 7000N |
| 050M62000 | 592580 | 2400N |
| 050M63000 | 592650 | 2400N |
| 050M123000 | 592680 | 10000N |
| 050M102000 | 592620 | 7000N |
| 050M83000 | 592660 | 4500N |
| 050M82000S4 | 592730 | 4500N |

Table 2/2

| Catalog Number | Article Number | Static Load |
|----------------|----------------|-------------|
| 050M62000S4 | 592710 | 2400N |
| 050M102000S4 | 592750 | 7000N |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

