

MTCA.4 Front Panel



AdvancedTCA front panel (stainless steel) for textile gasketing. Shielded filler modules are used to close unused slots.

CERTIFICATIONS



FEATURES

In accordance with MicroTCA.1 and MicroTCA.4 specifications

Shielded filler modules are used to close unused slots

Can be screwed on; is supported on the guide rail

SPECIFICATIONS

- Product Family:** AdvancedMC
- Accessory Type:** Front panel
- Type:** Front Panel
- Product Type:** Front Panel
- Material:** Stainless Steel
- EMC Shielding:** Yes

Table 1/2

| Catalog Number | Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|--------|------------|------------------|----------------|-------------|--------------|
| 20849-214 | 170mm | 2HP | 1 | Screw-on Front | Textile EMC | Raw |
| 20849-213 | 95mm | 2HP | 1 | Screw-on Front | Textile EMC | Raw |

| Catalog Number | Height | Rack Width | Package Quantity | Mounting | Gasket Type | Front Finish |
|----------------|---------|------------|------------------|----------------|-------------|--------------|
| 21850-102 | 84.68mm | | 1 | Screw-on Front | Textile EMC | Raw |
| 21850-103 | 84.68mm | | 1 | Screw-on Front | Textile EMC | Raw |

Table 2/2

| Catalog Number | Rear Finish | Depth | Width |
|----------------|-------------|-------|---------|
| 20849-214 | Raw | 0.6mm | 8.8mm |
| 20849-213 | Raw | 0.6mm | 8.8mm |
| 21850-102 | Raw | 1mm | 18.96mm |
| 21850-103 | Raw | 1mm | 28.98mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE