

Socket Strip, USA

Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with US outlets.



CERTIFICATIONS



FEATURES

Horizontal or vertical mounting

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m, with USA plug

Socket strips with USA sockets

Mounting height 1 U

115 V, 15 A

In accordance with UL-498

SPECIFICATIONS

Material: Aluminum; Polyamide

Color: Grey

Product Type: Socket Strip

Table 1/2

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|----------------|-------------|-----------------|------------------|------------|------------------|-------|
| 60110-242 | USA | 11 | Yes | 115V | 1 | 44mm |

| Catalog Number | Socket Type | Socket Quantity | Switched Outlets | Voltage AC | Package Quantity | Depth |
|----------------|-------------|-----------------|------------------|------------|------------------|-------|
| 60110-240 | USA | 11 | No | 115V | 1 | 44mm |
| 60110-241 | USA | 15 | No | 115V | 1 | 44mm |

Table 2/2

| Catalog Number | Finish | Length |
|----------------|----------|---------|
| 60110-242 | Anodized | 438.5mm |
| 60110-240 | Anodized | 438.5mm |
| 60110-241 | Anodized | 947.5mm |

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE