

Horizontal Rails Threaded Insert, M2.5



The threaded insert is a metal strip with thread M2.5 and allows the fixing of front panels.

CERTIFICATIONS



FEATURES

The collar screws used for fixing partial-width front panels must be 12.3 mm long

Usable for all horizontal rails

SPECIFICATIONS

- Works With:** Subracks; Cases
- Product Family:** EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
- Material:** Steel
- Product Type:** Threaded Insert
- Finish:** Zinc Plated

Table 1/1

| Catalog Number | Rack Width | Package Quantity | Length |
|----------------|------------|------------------|-----------|
| 34561-328 | 28HP | 1 | 146.82mm |
| 34561-363 | 84HP | 1 | 324.62mm |
| 34561-384 | 84HP | 1 | 431.3mm |
| 34561-342 | 42HP | 1 | 217.94mm |
| 34565-196 | 196HP | 1 | 1000.26mm |

| Catalog Number | Rack Width | Package Quantity | Length |
|----------------|------------|------------------|----------|
| 34561-320 | 20HP | 1 | 106.18mm |
| 34561-340 | 40HP | 1 | 207.78mm |

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE