

19" Drawer



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 15 kg

Optional writing surface

SPECIFICATIONS

- Static Load:** 15kg
- Product Type:** Cabinet/Rack Drawer
- Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Finish | Package Quantity | Color | Color Code | Front Finish |
|----------------|-------------|---------------|------------------|------------|------------|--------------|
| 20110-054 | 1U | Powder Coated | 1 | Light Grey | RAL 7035 | |
| 20110-061 | 1U | Powder Coated | 1 | | | Anodized |
| 20110-180 | 1U | Powder Coated | 1 | Black Grey | RAL 7021 | |
| 20110-056 | 3U | Powder Coated | 1 | Light Grey | RAL 7035 | |
| 20110-062 | 2U | Powder Coated | 1 | | | Anodized |

| Catalog Number | Rack Height | Finish | Package Quantity | Color | Color Code | Front Finish |
|----------------|-------------|---------------|------------------|------------|------------|--------------|
| 20110-181 | 2U | Powder Coated | 1 | Black Grey | RAL 7021 | |
| 20110-063 | 3U | Powder Coated | 1 | | | Anodized |
| 20110-055 | 2U | Powder Coated | 1 | Light Grey | RAL 7035 | |
| 20110-182 | 3U | Powder Coated | 1 | Black Grey | RAL 7021 | |

Table 2/2

| Catalog Number | Type | Works With |
|----------------|--------|--------------|
| 20110-054 | Drawer | 19" Cabinets |
| 20110-061 | Drawer | 19" Cabinets |
| 20110-180 | Drawer | 19" Cabinets |
| 20110-056 | Drawer | 19" Cabinets |
| 20110-062 | Drawer | 19" Cabinets |
| 20110-181 | Drawer | 19" Cabinets |
| 20110-063 | Drawer | 19" Cabinets |
| 20110-055 | Drawer | 19" Cabinets |
| 20110-182 | Drawer | 19" Cabinets |

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE