

Countersunk Screw



Countersunk screws are used for numerous mounting options in a subrack or desktop case.

CERTIFICATIONS



FEATURES

Countersunk screw

SPECIFICATIONS

Product Type: Screw

Table 1/2

| Catalog Number | Length | Material | Finish | Package Quantity | Thread Size | Height |
|----------------|--------|----------|---------------|------------------|-------------|--------|
| 24560-139 | 5mm | Steel | Zinc Plated | 100 | M4 | |
| 24560-183 | 12mm | Steel | Zinc Plated | 100 | M5 | |
| 24560-182 | 12mm | Steel | Zinc Plated | 4 | M5 | |
| 24560-145 | 14mm | Steel | Zinc Plated | 100 | M4 | |
| 24560-164 | 8mm | Steel | Nickel Plated | 100 | M2.5 | 4.7mm |
| 24560-158 | 7.7mm | Steel | Zinc Plated | 100 | M2.5 | |
| 21100-542 | 8mm | Steel | Nickel Plated | 100 | M3 | |
| 21100-429 | 8mm | Steel | Nickel Plated | 100 | M2.5 | |
| 21100-649 | 10mm | Steel | Zinc Plated | 100 | M2.5 | |

| CatalogNumber | Length | Material | Finish | Package Quantity | Thread Size | Height |
|---------------|--------|----------|---------------|------------------|-------------|--------|
| 21100-500 | 10mm | Steel | Nickel Plated | 100 | M2.5 | |
| 21100-507 | 12mm | Steel | Nickel Plated | 100 | M2.5 | |

Table 2/2

| Catalog Number | Type | Width | Works With | Thread Type | Torque |
|----------------|-------------------|-------|--------------|-------------|--------|
| 24560-139 | Countersunk Screw | | Front Panels | | 1.3N·m |
| 24560-183 | Countersunk Screw | | Front Panels | | 2.4N·m |
| 24560-182 | Countersunk Screw | | Front Panels | | 2.4N·m |
| 24560-145 | Countersunk Screw | | Front Panels | | 2.4N·m |
| 24560-164 | Countersunk Screw | 4.7mm | Front Panels | Metric | |
| 24560-158 | Countersunk Screw | | Front Panels | | |
| 21100-542 | Screw | | Front Panels | | |
| 21100-429 | Screw | | Front Panels | | |
| 21100-649 | Screw | | Front Panels | | |
| 21100-500 | Screw | | Front Panels | | |
| 21100-507 | Screw | | Front Panels | | |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE