

Security DVR and 19-inch Rack Equipment Cabinet Type 1, 4U, Black, Steel

Data Solutions

CATALOG NUMBER

DVR4U



These cabinets provide physical protection and access control to DVR, 19-inch equipment or other equipment. Mount the cabinet vertically or horizontally on any surface.

INDUSTRY STANDARDS

UL 508A Listed; Type 1

CSA; Type 1

NEMA/EEMAC; Type 1

IEC 60529 IP20

EIA 310-D (19-in. spacing for rack equipment)

FEATURES

Houses 19-inch or shelf-mount equipment

Top cover has tool-less removal, is captivated by door and secured by key-lock, providing easy access and installation

Solid top cover protects equipment from falling debris

Two standard models are 4 and 6 RU high

Radius corners give streamlined appearance and eliminate sharp edges

Solid front door has 180-degree opening continuous hinge

Quarter-turn keylock with two keys on door

Vented sides dissipate heat from equipment

A fan-ready cutout is provided on left side

14 gauge steel rack angles are adjustable within the cabinet body

Knockouts on bottom and side for data and power cables

Rubber feet provide secure placement and prevent scratches

PRODUCT ATTRIBUTES

Article Number: 17905

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 1.21mm

Rack Units: 4U

ADDITIONAL PRODUCT DETAILS

Velcro is a trademark of Velcro Industries B.V.

Reference spec sheet on Downloads tab for Vertical Cable Manager Selection Guide.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE