

Hex Nut



FEATURES

Internally threaded with a hex drive for many applications

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Rod Size	Thickness
010M6	592040	3535239	Steel	Electrogalvanized	M6	5 mm
010M8S4	592140	3534942	Stainless Steel 304 (EN 1.4301)		M8	6.5 mm
010M8	592050	3535241	Steel	Electrogalvanized	M8	6.5 mm
010M10HD	592065	3435969	Steel	Hot-Dip Galvanized	M10	8 mm
010M10S4	592150	3534944	Stainless Steel 304 (EN 1.4301)		M10	8 mm
010M12HD	592075	3435971	Steel	Hot-Dip Galvanized	M12	10 mm
010M12S4	592160	3534946	Stainless Steel 304 (EN 1.4301)		M12	10 mm

Catalog Number	Article Number	E-Number	Material	Finish	Rod Size	Thickness
010M12	592070	3535243	Steel	Electrogalvanized	M12	10 mm
010M16	400444		Steel	Electrogalvanized	M16	13 mm
010M10	592060	3535242	Steel	Electrogalvanized	M10	

Table 2/2

Catalog Number	Article Number	E-Number	Wire Size
010M6	592040	3535239	10 mm
010M8S4	592140	3534942	13 mm
010M8	592050	3535241	13 mm
010M10HD	592065	3435969	17 mm
010M10S4	592150	3534944	17 mm
010M12HD	592075	3435971	19 mm
010M12S4	592160	3534946	19 mm
010M12	592070	3535243	19 mm
010M16	400444		24 mm
010M10	592060	3535242	

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

