

nVent CADDY Cat HP J-Hook Angle Bracket, 4.7 mm Hole


Data Solutions

CATALOG NUMBER

CATHPAN



CERTIFICATIONS



FEATURES

Ideal for attaching to threaded rod, concrete, steel or wood surfaces

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook

PRODUCT ATTRIBUTES

Article Number: 181065


Material: Spring Steel

Finish: nVent CADDY Armour

Hole Size (HS): 4.7mm

Static Load: 712N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE