

# AccessPlus Rack Angles



The AccessPlus Rack Angles are used to mount 19in rack equipment inside the AccessPlus product. They have EIA universal spaced, 19-in. rack-mounting holes that are RU marked from bottom to top. The rack angle holes are either 10-32 tapped or square. Please note twenty mounting screws are included.

## FEATURES

---

The AccessPlus Rack Angles are used to mount 19in rack equipment inside the AccessPlus product

They have EIA universal spaced, 19-in. rack-mounting holes that are RU marked from bottom to top

The rack angle holes are either 10-32 tapped or square

Twenty mounting screws included

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Material	Finish	Thickness	Rack Units
EWMR60S	17897	Mild Steel	Zinc Plated	2.66mm	32U
EWMR24T	17887	Mild Steel	Zinc Plated	2.66mm	12U
EWMR72S	17898	Mild Steel	Zinc Plated	2.66mm	39U
EWMR36S	17895	Mild Steel	Zinc Plated	2.66mm	19U
EWMR24S	17894	Mild Steel	Zinc Plated	2.66mm	12U
EWMR36T	17888	Mild Steel	Zinc Plated	2.66mm	19U
EWMR60T	17892	Mild Steel	Zinc Plated	2.66mm	32U
EWMR48S	17896	Mild Steel	Zinc Plated	2.66mm	26U
EWMR16T	28685	Mild Steel	Zinc Plated	2.66mm	8U
EWMR72T	17893	Mild Steel	Zinc Plated	2.66mm	39U
EWMR48T	17891	Mild Steel	Zinc Plated	2.66mm	26U
EWMR16S	28686	Mild Steel	Zinc Plated	2.66mm	8U

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**