

# Basic PDU, EB0402, 400 VAC, 3-PH, 16 A

## Data Solutions

### CATALOG NUMBER

**EB0402**



Modular, compact PDU. Ultra-Low Profile Design

### FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

### PRODUCT ATTRIBUTES

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (24) C13; (6) C19

Socket Quantity: 30

Color: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 0

Input Cable Length: 3m

Input Cable Location: Top Feed

Input Voltage: 400V

Phase: 3 PH WYE

Interrupt Rating: 5kAIC

Max Power Input: 11.0 kVA

Amperage (Derated Amperage): 16 A

Output Voltage: 200 – 240VAC

Rack Units: 0U

Plug Type: IEC 60309 516P6 (IP44)

Metering Type: None

Removable Input Cable: No

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for vertical mounting separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**