

# Cable Channel



Cable ducting in side and rear cabinet areas and mounting on cabinet uprights, depth members or C-profiles.

## CERTIFICATIONS



## FEATURES

For cable ducting in side and rear cabinet areas

For mounting on cabinet uprights, depth members or C-profiles

## SPECIFICATIONS

**Product Type:** Cable Tray

Table 1/1

Catalog Number	Material	Package Quantity	Finish	Type	Cable Type	Certifications
60103-010	PVC	1		Cable Channel	Vertical	RoHS
60103-011	PVC	1		Cable Channel	Vertical	RoHS
24630-059	Steel	2	Powder Coated		Horizontal	
24630-058	Steel	2	Powder Coated		Horizontal	

## ADDITIONAL PRODUCT DETAILS

---

Please order assembly kit for cable channel separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**