

nVent CADDY EZ Riser



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

CERTIFICATIONS



FEATURES

Only one tool needed to tighten due to serrated wash-heads

Installs up to 60% faster than standard riser clamps

Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily

No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

| Catalog Number | Article Number | Outer Diameter (OD) | Hole Size (HS) | A | B | C |
|----------------|----------------|---------------------|----------------|----------|----------|---------|
| EZR0250 | 179231 | 73 mm | 9.9 mm | 279.4 mm | 190.5 mm | 25.4 mm |
| EZR0300 | 179232 | 88.9 mm | 9.9 mm | 298.5 mm | 206.4 mm | 25.4 mm |

| Catalog Number | Article Number | Outer Diameter (OD) | Hole Size (HS) | A | B | C |
|----------------|----------------|---------------------|----------------|----------|----------|---------|
| EZR0200 | 179230 | 60.3 mm | 9.9 mm | 260.4 mm | 177.8 mm | 25.4 mm |
| EZR0050 | 179225 | 21.3 mm | 9.9 mm | 215.9 mm | 130.2 mm | 22.2 mm |
| EZR0150 | 179229 | 48.3 mm | 9.9 mm | 250.8 mm | 158.8 mm | 22.2 mm |
| EZR0125 | 179228 | 42.2 mm | 9.9 mm | 241.3 mm | 152.4 mm | 22.2 mm |
| EZR0100 | 179227 | 33.4 mm | 9.9 mm | 228.6 mm | 142.9 mm | 22.2 mm |
| EZR0075 | 179226 | 26.7 mm | 9.9 mm | 228.6 mm | 136.5 mm | 22.2 mm |
| EZR0500 | 179235 | 141.3 mm | 13.2 mm | 368.3 mm | 298.5 mm | 38.1 mm |
| EZR0600 | 179236 | 168.3 mm | 13.2 mm | 406.4 mm | 323.9 mm | 38.1 mm |
| EZR0400 | 179234 | 114.3 mm | 13.2 mm | 330.2 mm | 254 mm | 31.8 mm |

Table 2/2

| Catalog Number | Article Number | Static Load |
|----------------|----------------|-------------|
| EZR0250 | 179231 | 1735N |
| EZR0300 | 179232 | 2400N |
| EZR0200 | 179230 | 1100N |
| EZR0050 | 179225 | 1100N |
| EZR0150 | 179229 | 1100N |
| EZR0125 | 179228 | 1100N |
| EZR0100 | 179227 | 1100N |
| EZR0075 | 179226 | 1100N |
| EZR0500 | 179235 | 5200N |
| EZR0600 | 179236 | 6900N |
| EZR0400 | 179234 | 3600N |

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

