

PropacPRO Tip-Up Handle

Tip-up carrying handle.



CERTIFICATIONS



FEATURES

Load-carrying capacity 20 kg

Can be locked in 30° increments

With powder-coated carrying bar

The handle enable a user to have a better view to the front side of the case in case of desktop usage

SPECIFICATIONS

- Material:** Aluminum; Zinc Alloy
- Works With:** Cases
- Product Type:** Handle
- Product Family:** PropacPRO

Table 1/1

| Catalog Number | Rack Width | Package Quantity | Handle Type |
|----------------|------------|------------------|---------------|
| 24576-071 | 42HP | 1 | Tip-up Handle |
| 24576-073 | 84HP | 1 | Tip-up Handle |
| 24576-072 | 63HP | 1 | Tip-up Handle |

ADDITIONAL PRODUCT DETAILS

To fit the tip-up carrying handle, holes must be drilled in the side panel.

Please select the preconfigured PropacPRO cases with holes for tip-up carrying handle.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE