

# Panel 19-inch Hinged Wall-Mount

## Data Solutions



The 19-inch Hinged Panel provides a solution for smaller network equipment, punch-downs and patch panels in areas where floor space is at a premium. Easy access facilitates component installation and future expansion without disturbing existing equipment or cabling. Can be mounted with hinges on left or right side.

### INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

### FEATURES

Open design offers unrestricted airflow

Large cable exit holes on back surface

Keyhole mounting slots on 16-in. centers accommodate up to 3/8- inch diameter mounting fasteners (not supplied)

Heavy duty hinges are welded to frame

Hinge provided for every two rack unit spacing

One rack unit model has half-size hinge

Provides access to rear of equipment

### SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
E19HPM1U	11001	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
E19HPM2U	11002	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
E19HPM4U	11003	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
E19HPM8U	11005	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm
E19HPM6U	11004	Mild Steel	Powder Coated	Jet Black	RAL 9005	2.66mm

Table 2/2

Catalog Number	Article Number	Rack Units	Load Rating
E19HPM1U	11001	1U	11.3kg
E19HPM2U	11002	2U	22.7kg
E19HPM4U	11003	4U	45.4kg
E19HPM8U	11005	8U	90.7kg
E19HPM6U	11004	6U	68kg

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**