

Heavy Duty Pipe Clamp per DIN 3567, Steel, HD, 508mm OD, 20" Pipe, 500 DN

CATALOG NUMBER

DIN508HD



FEATURES

For high static requirements in industrial construction

Suitable for fix point applications

Can be welded onto T-beam to form a sliding element

PRODUCT ATTRIBUTES

Article Number: 400239

Material: Steel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 508 mm

Pipe Size: 20"

NB/DN: 500


Hole Size (HS): 27 mm

Width (W): 70 mm

Thickness (T): 10 mm

A: 600 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

