

# Grounding/Grounding Clamp

## Data Solutions



These mechanical grounding clamps are designed for use with cable to bar in grounding and bonding systems. The Schroff grounding clamp allows a cross section of 100 mm<sup>2</sup>.

### CERTIFICATIONS



### FEATURES

Maximum cable cross-section 100 mm<sup>2</sup>

IBM-compatible grounding terminal for connecting a cabinet to the building ground

Surface tin-plated, in accordance with IBM Ref. No. 4716804

### SPECIFICATIONS

| Table 1/1      |              |            |          |                  |
|----------------|--------------|------------|----------|------------------|
| Catalog Number | Product Type | Finish     | Material | Package Quantity |
| 20118-030      | Clamp        | Galvanized | Aluminum | 1                |

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**