

# Motion detector

## Data Solutions



Motion detector: Prepared for mounting on door box, detection method: movement, detection fields of radar are adjustable, wide field 4 m (W) x 2 m (D), narrow field 2 m (W) x 2.5 m (D), supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate.

### CERTIFICATIONS



### FEATURES

Supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate

Wide field 4 m (W) x 2 m (D)

Arrow field 2 m (W) x 2.5 m (D)

Detection method: movement

Prepared for mounting on door box

Detection fields of radar are adjustable

### SPECIFICATIONS

Table 1/1

| Catalog Number | Type            | Works With        | Package Quantity |
|----------------|-----------------|-------------------|------------------|
| 60130-067      | Motion Detector | Aisle Containment | 1                |

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**