

# Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 500 kcmil Ropelay, Left Hand

## Data Solutions

### CATALOG NUMBER

**PBWT203SLH**



### FEATURES

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

### PRODUCT ATTRIBUTES

Material: Graphite; Steel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 500 kcmil Ropelay

Conductor Outer Diameter, Nominal: 26.42mm

Welder Style: T20

Orientation: Left Hand

Mold Only: No

Replacement Mold: PBW3SLH

Welding Material: PB250, Sold Separately

Handle Clamp: C105C, Sold Separately

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**