

Rubber Mount



The Vibration Isolation Mount line from nVent CADDY is used to minimize vibrations produced by supported systems such as mechanical equipment, pumps, ductwork, piping, and in-line, exhaust and cabinet fans.

FEATURES

Used to support HVAC equipment, air conditioning units, compressors, pumps, motors and fan pumps

Color coded for accurate selection and easy field verification

Rubber surface provides anti-skid properties

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load |
|----------------|----------------|---------|-----------|---------|----------------------|
| VIBRMA100 | 801419 | 44.45mm | 79.375mm | 31.75mm | 445N |
| VIBRMA060 | 801418 | 44.45mm | 79.375mm | 31.75mm | 267N |
| VIBRMA015 | 801416 | 44.45mm | 79.375mm | 31.75mm | 67N |
| VIBRMA030 | 801417 | 44.45mm | 79.375mm | 31.75mm | 134N |
| VIBRMB150 | 801421 | 60.33mm | 98.425mm | 44.45mm | 668N |
| VIBRMB200 | 801422 | 60.33mm | 98.425mm | 44.45mm | 890N |
| VIBRMB300 | 801423 | 60.33mm | 98.425mm | 44.45mm | 1335N |
| VIBRMB120 | 801420 | 60.33mm | 98.425mm | 44.45mm | 534N |
| VIBRMC200 | 801424 | 60.33mm | 101.6mm | 50.8mm | 890N |
| VIBRMC300 | 801425 | 60.33mm | 101.6mm | 50.8mm | 1335N |
| VIBRMC500 | 801427 | 60.33mm | 101.6mm | 50.8mm | 2224N |
| VIBRMC400 | 801426 | 60.33mm | 101.6mm | 50.8mm | 1780N |
| VIBRMD1000 | 801429 | 60.33mm | 149.225mm | 88.9mm | 4448N |

| Catalog Number | Article Number | Length | Width | Height | Ultimate Static Load |
|----------------|----------------|---------|-----------|--------|----------------------|
| VIBRMD1500 | 801430 | 60.33mm | 149.225mm | 88.9mm | 6672N |
| VIBRMD750 | 801428 | 60.33mm | 149.225mm | 88.9mm | 3336N |
| VIBRMD2200 | 801431 | 60.33mm | 149.225mm | 88.9mm | 9786N |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

