


Comline ECL 19"/23" Panel/Slide Mount Kit



Comline ECL 19"/23" Panel/Slide Mount Kit with load capacity of 400 kg, ensures easy fitting to depth members.

CERTIFICATIONS



FEATURES

Comline ECL 19"/23" Panel/Slide Mount Kit

For fitting to depth members(25 mm grid)

Load-carrying capacity 400 kg

Slide rails can be fitted

For recessed installation of 19"/23" components

SPECIFICATIONS

Product Type: Slide Mount

Material: Steel

Table 1/1

| Catalog Number | Rack Height | Height | Width | Package Quantity |
|----------------|-------------|--------|-------|------------------|
| 22349-024 | 12U | 660mm | 600mm | 2 |
| 22349-027 | 25U | 1220mm | 700mm | 2 |
| 22349-026 | 18U | 900mm | 700mm | 2 |
| 22349-025 | 18U | 900mm | 600mm | 2 |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE