We connect and protect

19" Front Panel, Vented, 2 U, 2.5 mm, Al, Untreated

Data Solutions

CATALOG NUMBER

30702-045





Vented front panels allows heat dissipation through holes.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

Vented front panels (Aluminum) allows heat dissipation

PRODUCT ATTRIBUTES

Rack Height: 2U
Accessory Type: Front panel
Finish: Anodized
Mounting: Screw-on Front
Package Quantity: 1
Front Finish: Raw

Rear Finish: Raw

EMC Shielding: No

Height (H): 88.1mm

Material: Aluminum

Product Type: Front Panel

Rack Width: 95HP

Type: 19" Front Panel

Width (W): 483mm

Net Weight: 0.247kg

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.