

Connection clamp with levers

Distribution Clamps for Distribution Box.



FEATURES

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm²

SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Color | Ambient Temperature | Clamp Quantity | Depth | Height |
|----------------|--------------|--------------------|---------------------|----------------|--------|--------|
| 20118-902 | Clamp | Transparent, Green | 85°C max | 3 | 18.8mm | 8.4mm |
| 20118-903 | Clamp | Transparent, Green | 85°C max | 5 | 18.8mm | 8.4mm |

Table 2/2

| Catalog Number | Material | Max Current | Max Voltage | Package Quantity | Weight | Width |
|----------------|---------------|-------------|-------------|------------------|--------|--------|
| 20118-902 | Polycarbonate | 20A | 600V | 10 | 2.5g | 18.8mm |
| 20118-903 | Polycarbonate | 20A | 600V | 10 | 4g | 30mm |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE