


Joint Bond T6 Complete Welder Pair, Signal, Head Free Bond Terminal Style, 5/16" Bondstrand

Data Solutions

CATALOG NUMBER

SBHFT6B



FEATURES

- Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint
- Connection is made within the confines of the splice bar
- Includes mold cleaner

PRODUCT ATTRIBUTES

- Material: Steel; Graphite; Thermoplastic
- Rail Type: 85 lb to 141 lb T-Rail Sections
- Bond Terminal Style: Head Free
- Conductor Size: 5/16" Bondstrand
- Conductor Outer Diameter, Nominal: 7.95mm
- Bond Length: 177.8mm
- Welder Style: T6
- Mold Only: No
- Replacement Mold: SBB492M

Welding Material: SB32, Sold Separately

Bond Clip: B194D x 2, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE