

Crimping Compression Tool, Foot Pump

Data Solutions

CATALOG NUMBER

M4FP



FEATURES

Wide cross section range

High-pressure 2 meter (6.5') long hose

Compact and easy to use

Includes easy-to-carry custom case

PRODUCT ATTRIBUTES

Applied Force: 56200lb

System: Foot pump hydraulic

Dies: PKM4 series

Crimping Shape: Hexagon

Conductor Size: #6 Stranded - 1000 kcmil Stranded; 16 mm² Stranded - 625 mm² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE