

19" Drawer, 2 U, Front Panel Anodized

Data Solutions

CATALOG NUMBER

20110-062



19" Drawers allow mounting of laptops, writing surfaces for easy operations. The SCHROFF 19" drawer has a load capacity of 15 KG, allowing a wide range of products to be assembled into the drawer.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 15 kg

Optional writing surface

PRODUCT ATTRIBUTES

Rack Height: 2U

Finish: Powder Coated

Package Quantity: 1

Front Finish: Anodized

Type: Drawer

Material: Steel

Product Type: Cabinet/Rack Drawer

Works With: 19" Cabinets

Net Weight: 8.1kg

ADDITIONAL PRODUCT DETAILS

Please order 19" assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE