

Rack-Mountable Tray 19-inch, 1Ux7.60, Black, Steel

Data Solutions

CATALOG NUMBER

A19FT3B



Fan trays enhance the natural convection airflow within a cabinet when installed with other 19-inch rack-mount equipment.

FEATURES

Fan trays available with either three or six 4-inch fans

Includes 72-inch (1829-mm) power cord with IEC 320 standard power socket

Power cord plugs into standard 115 VAC outlet

Lighted rocker switch provides on-off control and indicates when fans are on

PRODUCT ATTRIBUTES

Article Number: 13855

Height: 1.67in

Width: 19in

Fan Quantity: 3

Depth: 8.1in

Input Voltage AC: 100 – 120V

Nominal Watts: 45W

Temperature: 158°F max

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Color Code: RAL 9005

Thickness: 16ga

Weight: 10lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE