

Rack-Mount Shelf Solid 1000mm Max Depth, fits 19in Rack, Lt Gray, Steel

Data Solutions

CATALOG NUMBER

P19SH810



The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles. The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement. There are both solid and vented models available. They fit 19- or 23-inch rack spacing and require only 1U of rack space. Please note the load rating is for 150 lb. (68 kg).

FEATURES

The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles

The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement

There are both solid and vented models available

They fit 19- or 23-inch rack spacing and require only 1U of rack space

Please note the load rating is for 150 lb. (68 kg)

PRODUCT ATTRIBUTES

Article Number: 47409

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 14ga

Type: Solid

Length: 27.56in

Width: 17.32in

Max Depth: 38.58in

Fits Enclosure Depth: 39.37in max

Weight: 16.5lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE