

ProLine Server Cabinet

Data Solutions



The passively cooled ProLine Server Cabinet has a front viewing window and a wheeled base for application mobility and repositioning.

FEATURES

Front window door with key lock and vents offers visibility and ventilation

Open base with casters and levelers

Fully perforated rear door promotes airflow providing passive cooling to equipment

2000-mm tall cabinets have split rear perforated doors

Both front and rear doors provide security via lockable handles

Quick-release latches on side panels provide easy service access

Fully perforated top cover with two cable entry ports for easy access and service

Mounting channels provide infinite front-to-back adjustment of rack angles

SPECIFICATIONS

Material: Mild Steel

Finish: Powder Coated

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Color	Color Code
PSC1269B	48249	50.59in	23.94in	35.4in	Jet Black	RAL 9005
PSC12610B	48259	50.59in	23.94in	39.34in	Jet Black	RAL 9005
PSC20610	38969	82.08in	23.94in	39.34in	Light Gray	RAL 7035

Catalog Number	Article Number	Height	Width	Depth	Color	Color Code
PSC20610B	48279	82.08in	23.94in	39.34in	Jet Black	RAL 9005
PSC12610	46499	50.59in	23.94in	39.34in	Light Gray	RAL 7035
PSC1269	46509	50.59in	23.94in	35.4in	Light Gray	RAL 7035
PSC2069	35129	82.08in	23.94in	35.4in	Light Gray	RAL 7035
PSC20611B	14252	82.08in	23.94in	43.28in	Jet Black	RAL 9005
PSC2069B	48269	82.08in	23.94in	35.4in	Jet Black	RAL 9005
PSC20612	14255	82.08in	23.94in	47.22in	Light Gray	RAL 7035
PSC20612B	14254	82.08in	23.94in	47.22in	Jet Black	RAL 9005
PSC20611	14253	82.08in	23.94in	43.28in	Light Gray	RAL 7035

Table 2/2

Catalog Number	Article Number	Thickness	Rack Units	Additional Rack Angles
PSC1269B	48249	16ga	24U	PRA1912THL1
PSC12610B	48259	16ga	24U	PRA1912THL1
PSC20610	38969	16ga	42U	PRA1920THL1
PSC20610B	48279	16ga	42U	PRA1920THL1
PSC12610	46499	16ga	24U	PRA1912THL1
PSC1269	46509	16ga	24U	PRA1912THL1
PSC2069	35129	14ga	42U	PRA1920THL1
PSC20611B	14252	14ga	42U	PRA1920THL1
PSC2069B	48269	14ga	42U	PRA1920THL1
PSC20612	14255	14ga	42U	PRA1920THL1
PSC20612B	14254	14ga	42U	PRA1920THL1
PSC20611	14253	14ga	42U	PRA1920THL1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE