

Rack-Mount Adjustable Shelf

Data Solutions



The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles. The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement. There are both solid and vented models available. They fit 19- or 23-inch rack spacing and require only 1U of rack space. Please note the load rating is for 150 lb. (68 kg).

FEATURES

The Rack-Mount Adjustable Shelf mounts to the front surface of front and back rack angles

The adjustable shelf support brackets are clear-plated 12 gauge steel and adjustable to fit multiple-depth enclosures or rack angle placement

There are both solid and vented models available

They fit 19- or 23-inch rack spacing and require only 1U of rack space

Please note the load rating is for 150 lb. (68 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
P19SH810	47409	Mild Steel	Powder Coated	Light Gray	RAL 7035	14ga
P23SH810B	12956	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P19SH810B	47919	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P19SH68	47399	Mild Steel	Powder Coated	Light Gray	RAL 7035	14ga
P19VSH68B	11053	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P19SH68B	47909	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P23SH68B	12955	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P23VSH810B	11056	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga

CatalogNumber	Article Number	Material	Finish	Color	Color Code	Thickness
P23VSH68B	11055	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga
P19VSH810B	11054	Mild Steel	Powder Coated	Jet Black	RAL 9005	14ga

Table 2/2

Catalog Number	Article Number	Type	Length	Width	Max Depth	Fits Enclosure Depth
P19SH810	47409	Solid	27.56in	17.32in	38.58in	39.37in max
P23SH810B	12956	Solid	27.56in	21.32in	38.58in	39.37in max
P19SH810B	47919	Solid	27.56in	17.32in	38.58in	39.37in max
P19SH68	47399	Solid	19.68in	17.32in	30.71in	31.5in max
P19VSH68B	11053	Vented	19.68in	17.32in	30.71in	31.5in max
P19SH68B	47909	Solid	19.68in	17.32in	30.71in	31.5in max
P23SH68B	12955	Solid	19.68in	21.32in	30.71in	31.5in max
P23VSH810B	11056	Vented	27.56in	21.32in	38.58in	39.37in max
P23VSH68B	11055	Vented	19.68in	21.32in	30.71in	31.5in max
P19VSH810B	11054	Vented	27.56in	17.32in	38.58in	39.37in max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE