

# Varistar CP Server Cabinet

## Data Solutions



Welded steel frame for high static load requirements.  
Prepared for 19" integration of IT assets.

### FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

### SPECIFICATIONS

- Product Type:** Rack
- Cladding Color Code:** RAL 7021
- Frame Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Cladding Material | Cladding Color | Type     | Package Quantity | Dynamic Load |
|----------------|-------------|-------------------|----------------|----------|------------------|--------------|
| 10630-020      | 47U         | Steel             | Black Grey     | Standard | 1                | 2200lbf      |

| Catalog Number | Rack Height | Cladding Material | Cladding Color | Type         | Package Quantity | Dynamic Load |
|----------------|-------------|-------------------|----------------|--------------|------------------|--------------|
| 10630-019      | 47U         | Steel             | Black Grey     | Standard     | 1                | 2200lbf      |
| 10630-026      | 47U         | Steel             | Black Grey     | Side-by-Side | 1                | 2200lbf      |
| 10630-023      | 42U         | Steel             | Black Grey     | Side-by-Side | 1                | 2200lbf      |
| 10630-017      | 42U         | Steel             | Black Grey     | Standard     | 1                | 2200lbf      |
| 10630-018      | 42U         | Steel             | Black Grey     | Standard     | 1                | 2200lbf      |
| 10630-024      | 42U         | Steel             | Black Grey     | Side-by-Side | 1                | 2200lbf      |
| 10630-025      | 47U         | Steel             | Black Grey     | Side-by-Side | 1                | 2200lbf      |

Table 2/2

| Catalog Number | Finish        | Material |
|----------------|---------------|----------|
| 10630-020      | Powder Coated | Steel    |
| 10630-019      | Powder Coated | Steel    |
| 10630-026      | Powder Coated | Steel    |
| 10630-023      | Powder Coated | Steel    |
| 10630-017      | Powder Coated | Steel    |
| 10630-018      | Powder Coated | Steel    |
| 10630-024      | Powder Coated | Steel    |
| 10630-025      | Powder Coated | Steel    |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**