

Partial Height Swing Frames, SFCP



A partial height swing frame for 19" equipment that provides additional mounting space for such equipment, as well as rear access to the fitted components and equipment once opened.

FEATURES

Description: Partial height swing frame for 19"-components allowing left or right hand opening. Can be used in wall mounted, steel enclosures, and floor standing, combinable and compact, steel enclosures. Rigid S-shaped frame profile equipped with 19" hole pattern in front and back. Zinc plated frame for direct earthing of the mounted components. Standard opening angle 125°-155°. Mounting in wall mounted, steel enclosures requires the SFBP transversal support in combination with the AVB. Mounting in floor standing steel combinable enclosures requires the SFBP transversal support.

Lock: 1 double-bit 3 mm lock.

Material: 2 mm zinc plated steel.

Pack quantity: 1 swing frame with hinges.

Mounting requirements: Mounting in wall mounted, steel enclosures requires the SFBP transversal support in combination with the AVB. Mounting in floor standing steel combinable enclosures requires the SFBP transversal support. Adjustable in depth in combination with CLPK profiles.

SPECIFICATIONS

Thickness: 14ga
Material: Mild Steel
Finish: Zinc Plated

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Load Rating |
|----------------|----------------|---------|---------|--------|--------------------|-------------|
| SFCP066 | SFCP066 | 23.62in | 19.53in | 2.36in | Mild Steel | 300N |
| SFCP196 | SFCP196 | 39.37in | 35.28in | 2.36in | Mild Steel | 500N |
| SFCP106 | SFCP106 | 23.62in | 19.53in | 2.36in | Mild Steel | 500N |
| SFCP126 | SFCP126 | 31.5in | 27.4in | 2.36in | Mild Steel | 500N |
| SFCP246 | SFCP246 | 47.24in | 43.15in | 2.36in | Mild Steel | 500N |
| SFCP036 | SFCP036 | 23.62in | 19.53in | 2.36in | Mild Steel | 150N |
| SFCP156 | SFCP156 | 31.5in | 27.4in | 2.36in | Mild Steel | 500N |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE