

ProLine S1 Server Package

ProLine S1 Server Package Cabinets are an economical solution for contractors, small computer rooms, schools, retail outlets, or smaller networks that require a general purpose cabinet to house servers, switches, cables and other communication equipment. Multiple sizes, configurations, and accessories give ProLine S1 Cabinets wide application flexibility. ProLine S1 Server Packages are a data center-ready solution designed to be configured in a row or stand-alone configuration. The cabinets feature airflow management and provide easy cable access/mounting provisions.



INDUSTRY STANDARDS

UL 2416 Listed File Number E230874

cUL Listed per CSA 22.2 60950-1-07

UL 2416 Bonding and Grounding (with use of PGK grounding Kit)

EIA 310-D (RU – Rack Unit spacing, marking, and positioning)

IEC 60529, IP20

FEATURES

Top panel has four-corner brush strip cable entry

Internal airflow management

Cable management (750mm and 800mm wide models)

Plinth base

Ability to externally mount cable management (i.e. ladder rack)

Caster/leveler kit pre-installed

PDU mounting brackets included (qty 2 pair)

Joining kits included with “middle” configurations

SPECIFICATIONS

Material: Mild Steel
Finish: Powder Coated

Table 1/2

Catalog Number	Article Number	Height	Width	Depth	Color	Color Code
PS1SPM23612B	59074	93.03in	23.86in	47.17in	Jet Black	RAL 9005
PS1SPE23812W	59069	93.03in	31.81in	47.17in	Signal White	RAL 9003
PS1SPE21812W	59063	85.16in	31.81in	47.17in	Signal White	RAL 9003
PS1SPM21812W	59064	85.16in	31.81in	47.17in	Signal White	RAL 9003
PS1SPM237512W	59068	93.03in	29.72in	47.17in	Signal White	RAL 9003
PS1SPE23612B	59073	93.03in	23.86in	47.17in	Jet Black	RAL 9005
PS1SPE21612W	59057	85.16in	23.86in	47.17in	Signal White	RAL 9003
PS1SPE217512B	39233	85.14in	27.87in	47.17in	Jet Black	RAL 9005
PS1SPM23812B	59078	93.03in	31.81in	47.17in	Jet Black	RAL 9005
PS1SPM217512B	39234	85.14in	27.87in	47.17in	Jet Black	RAL 9005
PS1SPM21612B	39232	85.14in	23.87in	47.17in	Jet Black	RAL 9005
PS1SPM21812B	39236	85.14in	31.81in	47.17in	Jet Black	RAL 9005
PS1SPE23612W	59065	93.03in	23.86in	47.17in	Signal White	RAL 9003
PS1SPE237512W	59067	93.03in	29.72in	47.17in	Signal White	RAL 9003
PS1SPE21812B	39235	85.14in	31.81in	47.17in	Jet Black	RAL 9005
PS1SPE217512W	59059	85.16in	29.72in	47.17in	Signal White	RAL 9003
PS1SPM23612W	59066	93.03in	23.86in	47.17in	Signal White	RAL 9003
PS1SPE237512B	59075	93.03in	29.72in	47.17in	Jet Black	RAL 9005
PS1SPM217512W	59062	85.16in	29.72in	47.17in	Signal White	RAL 9003
PS1SPM23812W	59072	93.03in	31.81in	47.17in	Signal White	RAL 9003

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Color	Color Code
PS1SPM237512B	59076	93.03in	29.72in	47.17in	Jet Black	RAL 9005
PS1SPM21612W	59058	85.16in	23.86in	47.17in	Signal White	RAL 9003
PS1SPE21612B	39231	85.14in	23.87in	47.17in	Jet Black	RAL 9005
PS1SPE23812B	59077	93.03in	31.81in	47.17in	Jet Black	RAL 9005

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE