


# ProTek Rack Angles



The ProTek Rack Angles support 19in rack equipment in the single- and double-hinged ProTek product. The square- and tapped-hole rack angles support EIA spaced IT equipment that is to be mounted within a ProTek cabinet.

## FEATURES

---

The ProTek Rack Angles support 19in rack equipment in the single- and double-hinged ProTek product

The square- and tapped-hole rack angles support EIA spaced IT equipment that is to be mounted within a ProTek cabinet

## SPECIFICATIONS

Table 1/1

Catalog Number	Article Number	Height	Material	Finish	Thickness	Hole Type
PTRA24T	23772	21in	Mild Steel	Zinc Plated	12ga	Tapped
PTRA60T	23778	56in	Mild Steel	Zinc Plated	12ga	Tapped
PTRA16S	23771	14in	Mild Steel	Zinc Plated	12ga	Square
PTRA24S	23773	21in	Mild Steel	Zinc Plated	12ga	Square
PTRA48T	23776	45.5in	Mild Steel	Zinc Plated	12ga	Tapped
PTRA36T	23774	33.25in	Mild Steel	Zinc Plated	12ga	Tapped
PTRA48S	23777	45.5in	Mild Steel	Zinc Plated	12ga	Square
PTRA16T	23768	14in	Mild Steel	Zinc Plated	12ga	Tapped
PTRA60S	23781	56in	Mild Steel	Zinc Plated	12ga	Square
PTRA36S	23775	33.25in	Mild Steel	Zinc Plated	12ga	Square

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**