

PYROPAK TERMINATION KIT

nVent PYROTENAX Pyropak Termination Kit is a range of mineral insulated (MI) termination kits for 8 AWG and 10 AWG single conductor and all multiconductor copper sheathed cables. The cable end is sealed using either a mastic or epoxy sealing compound, depending on the temperature rating required. Each kit contains enough material to terminate two cable ends. To reduce installation time, MI wiring cables can be supplied with factory terminated ends, using brass gland connectors and epoxy sealed cable ends.

FEATURES & BENEFITS

Easy to use

Reliable during long life: 30 year product warranty available

SPECIFICATIONS

Voltage Rating ≤ 600 V

Max Operating Temperature 105 °C

Tail size 90 cm

Table 1/1

| Catalog Number | Suitable for Cable Type | Thread Size | Thread Type |
|----------------|-------------------------|-------------|-------------|
| PPK5 | 2/12-402 | 1/2" | NPT |
| PPK30 | 2/14-371 | 1/2" | NPT |
| PPK32 | 2/16-340 | 1/2" | NPT |
| PPK9 | 3/10-480 | 3/4" | NPT |
| PPK11 | 3/12-480 | 3/4" | NPT |
| PPK35 | 3/3-834 | 1-1/4" | NPT |
| PPK15 | 3/4-746 | 1-1/4" | NPT |
| PPK14 | 3/6-621 | 3/4" | NPT |
| PPK12 | 3/8-590 | 3/4" | NPT |
| PPK36 | 4/10-590 | 3/4" | NPT |

| Catalog Number | Suitable for Cable Type | Thread Size | Thread Type |
|----------------|-------------------------|-------------|-------------|
| PPK37 | 4/6-730 | 1-1/4" | NPT |

Voltage Rating ≤ 600 V

Max Operating Temperature 105 °C

Tail size 30 cm

Table 1/1

| Catalog Number | Suitable for Cable Type | Thread Size | Thread Type |
|----------------|-------------------------|-------------|-------------|
| PPK4 | 2/12-402 | 1/2" | NPT |
| PPK2 | 2/14-371 | 1/2" | NPT |
| PPK31 | 2/16-246T | 3/4" | NPT |
| PPK1 | 2/16-340 | 1/2" | NPT |
| PPK33 | 2/16-364TS | 3/4" | NPT |
| PPK34 | 2/18-215T | 1/2" | NPT |
| PPK6 | 2/18-324TS | 1/2" | NPT |
| PPK8 | 3/10-480 | 3/4" | NPT |
| PPK10 | 3/12-480 | 3/4" | NPT |
| PPK3 | 3/14-387 | 1/2" | NPT |
| PPK13 | 3/6-621 | 3/4" | NPT |
| PPK7 | 4/14-465 | 3/4" | NPT |

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
 thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2021 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.
 nVent reserves the right to change specifications without notice.