

Front Panel, Retrofit Shielding



Flat front panel. Shieldable with stainless steel EMC gasket.

CERTIFICATIONS



FEATURES

For stainless steel EMC gasket

Al, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Material:	Aluminum
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel without Handle
EMC Shielding:	No (Retrofittable)

Table 1/2

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Gasket Type	Front Finish
20846-436	3U	28HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-425	3U	3HP	1	Screw-on Front	Stainless Steel EMC	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Gasket Type	Front Finish
30846-588	2U	84HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-771	6U	84HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-448	6U	10HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-676	3U	84HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-430	3U	8HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-442	6U	3HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-456	6U	16HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-449	6U	12HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-434	3U	21HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-429	3U	7HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-426	3U	4HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-427	3U	5HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-454	6U	63HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-438	3U	63HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-453	6U	42HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-450	6U	14HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-452	6U	28HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-437	3U	42HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-451	6U	21HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-446	6U	7HP	1	Screw-on Front	Stainless Steel EMC	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Gasket Type	Front Finish
20846-431	3U	10HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-424	3U	16HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-445	6U	6HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-865	6U	2HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-428	3U	6HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-444	6U	5HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-864	3U	2HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-433	3U	14HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-432	3U	12HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-859	9U	84HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-447	6U	8HP	1	Screw-on Front	Stainless Steel EMC	Anodized
20846-443	6U	4HP	1	Screw-on Front	Stainless Steel EMC	Anodized
30846-683	4U	84HP	1	Screw-on Front	Stainless Steel EMC	Anodized

Table 2/2

Catalog Number	Rear Finish	Treated Edges	Complies With	Finish
20846-436	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-425	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
30846-588	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated
30846-771	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-448	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
30846-676	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized, Passivated

Catalog Number	Rear Finish	Treated Edges	Complies With	Finish
20846-430	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-442	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-456	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-449	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-434	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-429	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-426	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-427	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-454	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-438	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-453	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-450	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-452	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-437	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-451	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-446	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-431	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-424	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-445	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
30846-865	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized
20846-428	Conductive	No	IEC 60297-3-101, IEEE 1101.1/10	Anodized

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE