

Guide Rail With Coding for CompactPCI/ VME64x, PC



New generation of Wih Coding type guide rails for PCBs or plug-in units. Forms a reliable interface between the subrack mechanics and the sub-assemblies. With the optimized design and the new high quality plastic material not just the stability was significantly increased, but also the fire safety properties improved. Which means the material ensures a low flammability, low smoke toxicity and density and fulfills the EN 45545-2 (Fire Safety in Railway Vehicle) requirements sets R22, R23 and R24 with the

CERTIFICATIONS



FEATURES

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to a optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

Storage temperature: from -40 °C ... 130 °C

SPECIFICATIONS

Works With:	Subracks; Cases; 19" Chassis; Systems
Type:	Coding
Product Family:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type:	Guide Rail

Table 1/1

Catalog Number	Material	Color	Package Quantity	Complies With	Finish
64568-110	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1	EN 45545-2	
64568-085	Fiber-Reinforced Plastic	Red	1	EN 45545-2	
64568-112	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	1	EN 45545-2	
64568-111	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1	EN 45545-2	
64568-086	Fiber-Reinforced Plastic	Grey	1	EN 45545-2	
64568-109	Fiber-Reinforced Plastic, Aluminum	Red, Silver	1	EN 45545-2	
64568-091	Fiber-Reinforced Plastic	Red	1	EN 45545-2	
64568-090	Fiber-Reinforced Plastic	Grey	1	EN 45545-2	
64568-092	Fiber-Reinforced Plastic	Grey	1	EN 45545-2	
64568-089	Fiber-Reinforced Plastic	Red	1	EN 45545-2	
24568-360	Fiber-Reinforced Plastic	Grey	10	EN 45545-2	
24568-358	Fiber-Reinforced Plastic	Grey	10	EN 45545-2	
24568-357	Fiber-Reinforced Plastic	Red	10	EN 45545-2	
24568-356	Fiber-Reinforced Plastic	Red	10	EN 45545-2	
24568-332	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10	EN 45545-2	Anodized
24568-331	Fiber-Reinforced Plastic, Aluminum	Red, Silver	10	EN 45545-2	Anodized
24568-341	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10	EN 45545-2	Anodized
24568-342	Fiber-Reinforced Plastic, Aluminum	Grey, Silver	10	EN 45545-2	

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack

Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE