

Tray Handle

The tray handle can be clip into a cutout in the side panel of a case. 2 sizes available.



CERTIFICATIONS



FEATURES

Static load-carrying capacity 30 kg/pair

Side panel thickness min. 1,0 mm

SPECIFICATIONS

Color:	Black
Works With:	Cases
Product Family:	RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec
Product Type:	Handle
Material:	Polycarbonate
Type:	Static

Table 1/1

Catalog Number	Package Quantity	Handle Type	Flammability Rating
60225-012	1	Tray Handle	UL® 94V-0
60229-004	1	Tray Handle	UL® 94V-0

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE