


Operator Interface Control Panel, OICP



The aluminium operator interface control panel, OICP, has a pre-machined hole pattern to allow for the desired fixation to a swing arm, plus a removable front plate at a IP 65 protection degree. Components can be easily fitted thanks to the removable front plate, but will also be easily accessible through a removable rear panel. Side handles on the enclosure allow for easy movement of the enclosure into the desired working position. The aluminium body will dissipate more heat than a mild steel body, which may eliminate the need for additional ventilation.

INDUSTRY STANDARDS

CE UKCA

GOST

FEATURES

Material: Body: Al Mg Si05. Rear plate: Al Mg. Corners: AISI 12.

Protection: IP 65.

Finish: Body and rear plate: anodised aluminium. Corners: RAL 7016.

Mounting requirements: OIFP front panel is not included in the standard delivery and needs to be ordered separately.

Delivery: Body, screwed rear plate, front plate mounting kit, and mounting accessories.

SPECIFICATIONS

Material:	Aluminum
Color:	Anthracite Gray
Finish:	Powder Coated
Color Code:	RAL 7016

Table 1/1

Catalog Number	Height	Width	Depth	Weight
OICP343920	345mm	395mm	200mm	7kg
OICP395220	398mm	525mm	200mm	9kg
OICP305220	309mm	525mm	200mm	7.9kg
OICP355220	345mm	525mm	200mm	8.3kg
OICP495420	495mm	542mm	200mm	10.3kg
OICP414720	415mm	470mm	200mm	8.5kg

ADDITIONAL PRODUCT DETAILS

The external enclosure dimension is increased by 16.5 mm, on the side where there is a grip profile.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE